

780 Keypad Feature Update July 2007

Version 101 Firmware Update

Effective July 2007, all 780 Keypad Demonstrator Modules are being manufactured with Version 101 (6/22/07) firmware. This version is an update from the Version 100 (12/21/05) firmware previously shipped and contains new features.

Features

Cancel/Verify Operation

When using an All/Perimeter or Home/Sleep/Away arming system, the 780 now demonstrates Cancel/Verify operation. This replaces the previous DISARM/SILENCE operation.

While armed, pressing the far left top row Select key simulates a front door zone fault and starts the entry delay.

After 10 seconds, the keypad displays FRONT ENTRY DOOR alarm. Entering any 4-digit code displays CANCEL VERIFY. Press the Select key under CANCEL to turn off the Red keypad backlighting and silence the alarm. ALARM CANCELED is displayed. Press the Select key under VERIFY to silence the alarm only. ALARM VERIFIED is displayed.




Shortcut Keys

The 780 now supports the LCD keypad one button shortcut keys. Holding down a keypad button for two seconds until the tone resounds allows you to arm, monitor, or reset your system. These options can still be accessed through the User Menu if desired.


Keypad Shortcut Keys

Keypad Key	Arming System Operation
Press Key 1	Arm Away for Home/Sleep/Away systems Arm All for All/Perimeter systems
Press Key 2	Sensor (Fire) Reset on all systems
Press Key 3	Arm Home for Home/Sleep/Away systems
Press Key 5	Monitor (Chime) on all systems
Press Key 6	Arm Perimeter for All/Perimeter systems
Press Key 7	Arm Sleep for Home/Sleep/Away systems



Ordering the New Firmware

To receive the updated Version 101 (6/22/07) firmware, return the 780 module to DMP and simply indicate "Update to Version 101" on the RMA tag. If a module is returned for other repair needs, this update will be done automatically as a standard part of the repair. If you need RMA tags, contact DMP Customer Service at 1-800-641-4282.



Digital Monitoring Products